



Launching instruction on steelplate for 4-35DK+ in cradle

Material no.: 1055968



Launching instruction on steel plate for throw overboard liferafts in cradle - either 4DK+, 6DK+, 8DK+, 10DK+, 12DK+, 16DK+, 20DK+, 25DK+ or 35DK+ in round container (SOLAS A and B).

Stainless steel launching plates made in 1 mm SUS316 stainless steel. A4 paper size with 4 mm holes in each corner. The hole centers are 5 mm from the sides/top/bottom.